

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430165

Status:

Active

Overview:

Heavy-Duty Industrial Wiring Devices

Description:

Super-Safeway Ground Fault Monitoring Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-15, 125V



Series image - Reference only

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E38085
General	
Product Family	Wiring Devices
Series	130143
IP Rating	N/A
NEMA Configuration	NEMA 5-15
Overview	Heavy-Duty Industrial Wiring Devices
Product Name	Super-Safeway
Receptacle Type	Single
Specialty	Monitoring
Type	Cordset
UPC	78678829858
Physical	
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Locking Blade	No
Net Weight	111.000/g
Poles	2-pole/3-wire
Electrical	
Cord Type	12/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	Yes
Voltage - Maximum	125V
Material Info	
Engineering Number	1547GCMA163

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

China RoHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301430165