

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430169

Status:

Active

Overview:

Heavy-Duty Industrial Wiring Devices

Description:

Super-Safeway Cordset 16 Gauge SOOW with Lock Blade, 3 Pole/3 Wire, Cordset Length 7.62m (25.0'), Non-NEMA, 15A/125V, 10A/250V

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E38085

General

Product Family

Series

IP Rating

NEMA Configuration

Overview

Product Name

Receptacle Type

Specialty

Type

UPC

Wiring Devices

130143

N/A

Non-NEMA Locking

Heavy-Duty Industrial Wiring Devices

Super-Safeway

Single

N/A

Cordset

78678879561

Physical

Flange

Flip Lid

Gender

Length

Locking Blade

Net Weight

Poles

No

No

Male-Female

7.62m (25.0')

Yes

444.000/kg

3-pole/3-wire

Electrical

Cord Type

Current - Maximum per Contact

GFCI

Lighted Connector

Voltage - Maximum

14/3 SOOW

10.0A, 15.0A

No

No

125V / 250V

Material Info

Engineering Number

2407A143



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301430169