

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301430196](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 30.48m (100.0'), NEMA L5-15, 125V

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR6837
UL E38085

General

Product Family Wiring Devices
Series [130143](#)
IP Rating IP67
NEMA Configuration NEMA L5-15
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
Product Name Watertite
Receptacle Type Single
Specialty N/A
Type Cordset
UPC 78678897144

Physical

Cord Grip Body Size F2 1/2"
Flange No
Flip Lid No
Gender Male-Female
Length 30.48m (100.0')
Locking Blade Yes
Net Weight 399.000/g
Poles 2-pole/3-wire

Electrical

Cord Type 12/3 SOOW
Current - Maximum per Contact 15.0A
GFCI No
Lighted Connector No
Voltage - Maximum 125V

Material Info

Engineering Number 24W47D163

Reference - Drawing Numbers

Sales Drawing 1301430187-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130143](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301430196