

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430217

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Cordset 14 Gauge SOOW, 3 Pole/3 Wire, Cordset Length 7.62m (25.0'), Non-NEMA, 250V

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

UL

E38085

General

Product Family

Wiring Devices

Series

130143

IP Rating

IP67

NEMA Configuration

Non-NEMA

Overview

Watertite Extreme Wet-Location Wiring Solutions

Product Name

Watertite Extreme

Receptacle Type

Single

Specialty

N/A

Type

Cordset

UPC

78678899030

Physical

Cord Grip Body Size

F3 3/4"

Flange

No

Flip Lid

No

Gender

Male-Female

Length

7.62m (25.0')

Locking Blade

No

Net Weight

211.000/kg

Poles

3-pole/3-wire

Electrical

Cord Type

14/3 SOOW

Current - Maximum per Contact

20.0A

GFCI

No

Lighted Connector

No

Voltage - Maximum

250V

Material Info

Engineering Number

26W08A143



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301430217](#)