

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301430308](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Cordset 12 Gauge SOOW, 4 Pole/5 Wire, Cordset Length 30.48m (100.0'), NEMA L21-20, 3Ø 208V

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR6837

General
Product Family Wiring Devices
Series [130143](#)
IP Rating IP67
NEMA Configuration NEMA L21-20
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
Product Name Watertite
Receptacle Type Single
Specialty N/A
Type Cordset
UPC 78678810306

Physical
Cord Grip Body Size F3 3/4"
Flange No
Flip Lid No
Gender Male-Female
Length 30.48m (100.0')
Locking Blade Yes
Net Weight 777.000/kg
Poles 4-pole/5-wire

Electrical
Cord Type 12/3 SOOW
Current - Maximum per Contact 20.0A
GFCI No
Lighted Connector No
Voltage - Maximum 3Ø 208V

Material Info
Engineering Number 26W81D125



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130143](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301430308