

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301460016

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Cordset 16 Gauge SOOW, 3 Pole/3 Wire, Cordset Length 7.62m (25.0'), Non-NEMA 15A/125V, 10A/250V



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)

Agency Certification	
CSA	LR6837
UL	E38085
General	
Product Family	Wiring Devices
Series	130146
IP Rating	IP67
NEMA Configuration	Non-NEMA
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Type	Cordset
UPC	78678898069
Physical	
Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Locking Blade	No
Net Weight	0.752/kg
Poles	3-pole/3-wire
Electrical	
Cord Type	16/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V
Material Info	
Engineering Number	14W07A163
Reference - Drawing Numbers	
Sales Drawing	1301460016-000

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130146 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301460016