

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460032](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Plug 2 Pole/3 Wire, NEMA 5-15, 125V, Cord Grip Body Size F2, Black, Silicone Husk

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

Agency Certification

CSA LR6837
UL E10176

General

Product Family Wiring Devices
Series [130146](#)
IP Rating IP69K
NEMA Configuration NEMA 5-15
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
Product Name Watertite Extreme
Receptacle Type N/A
Specialty N/A
Type Plug
UPC 78678871048

Physical

Cord Grip Body Size F2 1/2"
Flange No
Flip Lid No
Gender Male
Length N/A
Locking Blade No
Net Weight 45.620/g
Poles 2-pole/3-wire

Electrical

Cord Type N/A
Current - Maximum per Contact 15.0A
GFCI No
Lighted Connector No
Voltage - Maximum 125V

Material Info

Engineering Number 14W47BLK

Reference - Drawing Numbers

Sales Drawing 1301460031-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130146](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301460032](#) [14W47BLK](#)