

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460114](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Male Receptacle with Single Flip Coverplate, 3 Pole/3 Wire, Non-NEMA 15A/125V, 10A/250V

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Wiring Devices
Series	130146
IP Rating	IP67
NEMA Configuration	Non-NEMA
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Type	Inlet
UPC	78678871427
Physical	
Flange	No
Flip Lid	Yes
Gender	Male
Length	N/A
Locking Blade	No
Poles	3-pole/3-wire
Electrical	
Cord Type	N/A
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V
Material Info	
Engineering Number	59W07



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130146](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301460114