

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470015](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Plug with Locking Blade, 4 Pole/4 Wire, Non-NEMA, 208V, Cord Grip Body Size F4

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification	
CSA	LR6837
UL	E10176
General	
Product Family	Wiring Devices
Series	130147
IP Rating	IP67
NEMA Configuration	Non-NEMA
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	N/A
Specialty	N/A
Type	Plug
UPC	78678871291
Physical	
Cord Grip Body Size	F4 1"
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Locking Blade	Yes
Net Weight	390.996/g
Poles	4-pole/4-wire
Electrical	
Cord Type	N/A
Current - Maximum per Contact	20.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	208V
Material Info	
Engineering Number	26W09
Reference - Drawing Numbers	
Sales Drawing	1301470015-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130147](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301470015 26W09