

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470025](#)
Status: **Active**
Overview: [Watertite Wet-Location Wiring Solutions](#)
Description: Watertite Plug with Locking Blade, 3 Pole/4 Wire, NEMA L14-20, 250V, Cord Grip Body Size F3

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family [Wiring Devices](#)
 Series [130147](#)
 IP Rating IP67
 NEMA Configuration NEMA L14-20
 Overview [Watertite Wet-Location Wiring Solutions](#)
 Product Name Watertite
 Receptacle Type N/A
 Specialty N/A
 Type Plug
 UPC 78678871213

Physical

Cord Grip Body Size F3 3/4"
 Flange No
 Flip Lid No
 Gender Male
 Length N/A
 Locking Blade Yes
 Net Weight 233.599/g
 Poles 3-pole/4-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 20.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 250V

Material Info

Engineering Number 26W74

Reference - Drawing Numbers

Sales Drawing 1301470025-000



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130147 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301470025](#) [26W74](#)