

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470026](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Extra Hard Outdoor Plug With Locking Blade, 3 Pole/4 Wire, NEMA L14-20, 250V, Cord Grip Body Size F3, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR6837
UL E10176

General

Product Family Wiring Devices
Series [130147](#)
IP Rating IP67
NEMA Configuration NEMA L14-20
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
Product Name Watertite Extreme
Receptacle Type N/A
Specialty N/A
Type Plug
UPC 78678871341

Physical

Cord Grip Body Size F3 3/4"
Flange No
Flip Lid No
Gender Male
Length N/A
Locking Blade Yes
Poles 3-pole/4-wire

Electrical

Cord Type N/A
Current - Maximum per Contact 20.0A
GFCI No
Lighted Connector No
Voltage - Maximum 250V

Material Info

Engineering Number 26W74BLK

Reference - Drawing Numbers

Sales Drawing 1301470025-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130147](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301470026