

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301470052

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Connector for Male Receptacle with Locking Blade, 2 Pole/3 Wire, NEMA L7-20 277V, F3

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

Agency Certification

CSA

LR6837

General

Product Family

Series

IP Rating

NEMA Configuration

Overview

Product Name

Receptacle Type

Specialty

Type

UPC

Wiring Devices

130147

IP67

NEMA L7-20

Watertite Extreme Wet-Location Wiring Solutions

Watertite Extreme

Single

N/A

Connector

78678871370

Physical

Cord Grip Body Size

Flange

Flip Lid

Gender

Length

Locking Blade

Net Weight

Poles

F3 3/4"

No

No

Female

N/A

Yes

279.866/g

2-pole/3-wire

Electrical

Cord Type

Current - Maximum per Contact

GFCI

Lighted Connector

Voltage - Maximum

N/A

20.0A

No

No

277V

Material Info

Engineering Number

27W49MB

Reference - Drawing Numbers

Sales Drawing

1301470052-000



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130147 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301470052