

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301470096](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** Watertite Extreme Connector with Locking Blade, 2 Pole/3 Wire, NEMA L6-30, 125V, Cord Grip Body Size F4

**Documents:**  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

|                                    |                                                                 |
|------------------------------------|-----------------------------------------------------------------|
| <b>Agency Certification</b>        |                                                                 |
| CSA                                | LR6837                                                          |
| UL                                 | E10176                                                          |
| <b>General</b>                     |                                                                 |
| Product Family                     | Wiring Devices                                                  |
| Series                             | <a href="#">130147</a>                                          |
| IP Rating                          | IP67                                                            |
| NEMA Configuration                 | NEMA L6-30                                                      |
| Overview                           | <a href="#">Watertite Extreme Wet-Location Wiring Solutions</a> |
| Product Name                       | Watertite Extreme                                               |
| Receptacle Type                    | Single                                                          |
| Specialty                          | N/A                                                             |
| Type                               | Connector                                                       |
| UPC                                | 78678871332                                                     |
| <b>Physical</b>                    |                                                                 |
| Cord Grip Body Size                | F4 1"                                                           |
| Flange                             | No                                                              |
| Flip Lid                           | No                                                              |
| Gender                             | Female                                                          |
| Length                             | N/A                                                             |
| Locking Blade                      | Yes                                                             |
| Net Weight                         | 439.980/g                                                       |
| Poles                              | 2-pole/3-wire                                                   |
| <b>Electrical</b>                  |                                                                 |
| Cord Type                          | N/A                                                             |
| Current - Maximum per Contact      | 30.0A                                                           |
| GFCI                               | No                                                              |
| Lighted Connector                  | No                                                              |
| Voltage - Maximum                  | 250V                                                            |
| <b>Material Info</b>               |                                                                 |
| Engineering Number                 | 29W48                                                           |
| <b>Reference - Drawing Numbers</b> |                                                                 |
| Sales Drawing                      | 1301470096-000                                                  |



Series image - Reference only

|                                                                                                                                           |                   |
|-------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                                                                                                      |                   |
| <b>EU RoHS</b><br><b>Not Reviewed</b><br><b>REACH SVHC</b><br>Not Reviewed<br><b>Halogen-Free</b><br><b>Status</b><br><b>Not Reviewed</b> | <b>China RoHS</b> |
| For more information, please visit <a href="#">Contact US</a>                                                                             |                   |
| China ROHS                                                                                                                                | Not Reviewed      |
| ELV                                                                                                                                       | Not Relevant      |
| RoHS Phthalates                                                                                                                           | Not Reviewed      |

**Search Parts in this Series**  
[130147](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301470096 29W48