

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301470120

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Connector with Locking Blade, 4 Pole/5 Wire, NEMA L23-30, 3ø 600V, Cord Grip Body Size F4

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

Agency Certification

CSA

LR6837

UL

E10176

General

Product Family

Wiring Devices

Series

130147

IP Rating

IP67

NEMA Configuration

NEMA L23-30

Overview

Watertite Extreme Wet-Location Wiring Solutions

Product Name

Watertite Extreme

Receptacle Type

Single

Specialty

N/A

Type

Connector

UPC

78678871339

Physical

Cord Grip Body Size

F4 1"

Flange

No

Flip Lid

No

Gender

Female

Length

N/A

Locking Blade

Yes

Poles

4-pole/5-wire

Electrical

Cord Type

N/A

Current - Maximum per Contact

30.0A

GFCI

No

Lighted Connector

No

Voltage - Maximum

3Ø 600V

Material Info

Engineering Number

29W83

Reference - Drawing Numbers

Sales Drawing

1301470120-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130147 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301470120