

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301470123

Status:


Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Receptacle Flip Coverplate with California Style Locking Blade, 3 Pole/4 Wire, Non-NEMA, 250V



Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E68122
General	
Product Family	Wiring Devices
Series	130147
IP Rating	IP67
NEMA Configuration	Non-NEMA Locking
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Type	Receptacle
UPC	78678834846
Physical	
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Locking Blade	Yes
Poles	3-pole/4-wire
Electrical	
Cord Type	N/A
Current - Maximum per Contact	50.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V
Material Info	
Engineering Number	65W64

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130147 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301470123