

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470169](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 2 Pole/3 Wire, NEMA L6-30, 250V

Documents:

3D Model	Brochure (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Drawing (PDF)	

Agency Certification

CSA	LR6837
UL	E68122

General

Product Family	Wiring Devices
Series	130147
IP Rating	IP67
NEMA Configuration	NEMA L6-30
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Type	Receptacle
UPC	78678871575

Physical

Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Locking Blade	Yes
Poles	2-pole/3-wire

Electrical

Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V

Material Info

Engineering Number	69W48
--------------------	-------

Reference - Drawing Numbers

Sales Drawing	1301470169-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series

[130147](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301470169 69W48