

6


5

4

3

2

1

**TECHNICAL:**

LISTED:
RATED SUPPLY VOLTAGE:
RATED CURRENT:
RESET TYPE:
OPERATING FREQUENCY:
TYPE:
GROUND TRIP CURRENT:
OVERLOAD CURRENT:
INSULATION VOLTAGE:
ENDURANCE OPERATIONS:

UL AND cUL
120 VAC
UP TO 15 AMPS OR CABLE RATING
AUTOMATIC OR MANUAL
60 Hz
CLASS A
4-6 mA
90 AMP 125 VAC
1,500 VRMS - 1 MINUTE
3000 OPERATIONS

INITIAL RELEASE
EC NO: IGC2013-1078
DRWN: HRUIZ01 2013/02/06
CHKD: HKNEELAN 2014/07/22
APPR: JFMURPHY 2015/04/20

QUALITY
SYMBOLS
▽=0
▽C=0

**GENERAL TOLERANCES
(UNLESS SPECIFIED)**

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±.005
2 PLACES	±0.13	±0.010
1 PLACE	±0.25	±0.020

ANGULAR ±1/2°

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

MATERIAL NO.	ENGINEERING NO.	LENGTH "L"	LENGTH "A"	POWER-UP
1301530020	15050-1A	2 FT 7.5 IN	1 FT ± 1 IN	AUTO
1301530037	15050-6A	7 FT 7.5 IN	6 FT ± 2 IN	AUTO
1301530023	15050-25A	26 FT 7.5 IN	25 FT ± 2 IN	AUTO
1301530031	15050-50A	51 FT 7.5 IN	50 FT ± 4 IN	AUTO
1301530021	15050-1M	2 FT 7.5 IN	1 FT ± 1 IN	MANUAL
1301530038	15050-6M	7 FT 7.5 IN	6 FT ± 2 IN	MANUAL
1301530024	15050-25M	25 FT 7.5 IN	25 FT ± 2 IN	MANUAL
1301530032	15050-50M	50 FT 7.5 IN	50 FT ± 4 IN	MANUAL

DIMENSION STYLE
INCH

SCALE
NTS

DESIGN UNITS
INCH

THIRD ANGLE
PROJECTION

DRAWN BY DATE
HRUIZ01 2013/02/06

CHECKED BY DATE
HKNEELAN 2014/07/22

APPROVED BY DATE
JFMURPHY 2015/04/20

MATERIAL NO.
SEE TABLE

SIZE
A

TITLE
120V 15A INLINE GFCI
W/ MOLDED PLUG & CONN
NEMA 5-15

MOLEX INCORPORATED

DOCUMENT NO.
SD-130153-013

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301530031