





TECHNICAL:
LISTED:
RATED SUPPLY VOLTAGE:
RATED CURRENT:
RESET TYPE:
OPERATING FREQUENCY:
TYPE:
GROUND TRIP CURRENT:
OVERLOAD CURRENT:
INSULATION VOLTAGE:
ENDURANCE OPERATIONS:

UL AND cUL
120 VAC
UP TO 15 AMPS OR CABLE RATING
AUTOMATIC OR MANUAL
60 Hz
CLASS A
4-6 mA
90 AMP 125 VAC
1,500 VRMS – 1 MINUTE
3000 OPERATIONS

MATERIAL NO.	ENGINEERING NO.	LENGTH "L"	POWER-UP
1301530075	15053-2A	2 FT ± 1 IN	AUTO
1301530073	15053-25A	25 FT ± 2 IN	AUTO
1301530078	15053-50A	50 FT ± 4 IN	AUTO
1301530076	15053-2M	2 FT ± 1 IN	MANUAL
1301530074	15053-25M	25 FT ± 2 IN	MANUAL
1301530079	15053-50M	50 FT ± 4 IN	MANUAL

INITIAL RELEASE EC NO: IPG2013-1078 DRWN: HRUIZ01 2013/02/08 CHKD: HKNEELAN 2014/07/22 APPR: JFMURPHY 2015/04/20		DESCRIPTION REV	QUALITY SYMBOL	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE INCH		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION											
			 =0  =0		mm	INCH	DRAWN BY HRUIZ01	DATE 2013/02/08	TITLE 120V 15A GFCI PLUG W/ RCPT BOX NEMA 5-15													
				4 PLACES	±---	±---	CHECKED BY HKNEELAN	DATE 2014/07/22														
				3 PLACES	±---	±.005	APPROVED BY JFMURPHY								DATE 2015/04/20							
				2 PLACES	±0.13	±.010																
				1 PLACE	±0.25	±.020	MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-130153-019				SHEET NO. 1 OF 1									
			ANGULAR ±1/2°			MOLEX INCORPORATED																
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301530073