



TECHNICAL:
LISTED:
RATED SUPPLY VOLTAGE:
RATED CURRENT:
RESET TYPE:
OPERATING FREQUENCY:
TYPE:
GROUND TRIP CURRENT:
OVERLOAD CURRENT:
INSULATION VOLTAGE:
ENDURANCE OPERATIONS:

UL AND cUL
120 VAC
UP TO 15 AMPS OR CABLE RATING
AUTOMATIC OR MANUAL
60 Hz
CLASS A
4-6 mA
90 AMP 125 VAC
1,500 VRMS – 1 MINUTE
3000 OPERATIONS

INITIAL RELEASE EC NO: IPG2013-1078 DRWN: HRUIZ01 2013/02/08 CHK'D: HKNEELAN 2014/07/22 APPR: JFMURPHY 2015/04/20			DESCRIPTION	QUALITY SYMBOL <div>▽=0</div> <div>▽C=0</div>	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE INCH		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
						mm	INCH	DRAWN BY HRUIZ01		DATE 2013/02/08	TITLE 120V 15A GFCI PLUG W/ RCPT BOX NEMA 5-15			
					4 PLACES	±---	±---	CHECKED BY HKNEELAN		DATE 2014/07/22				
					3 PLACES	±---	±.005	APPROVED BY JFMURPHY		DATE 2015/04/20	MOLEX INCORPORATED			
					2 PLACES	±0.13	±.010							
					1 PLACE	±0.25	±.020	MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-130153-019		SHEET N 1 OF		
					ANGULAR ±1/2°									
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									
A			REV		SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

MATERIAL NO.	ENGINEERING NO.	LENGTH "L"	POWER-UP
1301530075	15053-2A	2 FT ± 1 IN	AUTO
1301530073	15053-25A	25 FT ± 2 IN	AUTO
1301530078	15053-50A	50 FT ± 4 IN	AUTO
1301530076	15053-2M	2 FT ± 1 IN	MANUAL
1301530074	15053-25M	25 FT ± 2 IN	MANUAL
1301530079	15053-50M	50 FT ± 4 IN	MANUAL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301530076