


J
I
H
G
F
E
D
C
B
A



TECHNICAL:
LISTED:
RATED SUPPLY VOLTAGE:
RATED CURRENT:
RESET TYPE:
OPERATING FREQUENCY:
TYPE:
GROUND TRIP CURRENT:
OVERLOAD CURRENT:
INSULATION VOLTAGE:
ENDURANCE OPERATIONS:

UL AND cUL
120 VAC
UP TO 15 AMPS OR CABLE RATING
AUTOMATIC OR MANUAL
60 Hz
CLASS A
4-6 mA
90 AMP 125 VAC
1,500 VRMS – 1 MINUTE
3000 OPERATIONS

INITIAL RELEASE EC NO: IPG2013-1078 DRWN: HRUIZ01 2013/02/08 CHK'D: HKNEELAN 2014/07/22 APPR: JFMURPHY 2015/04/20	DESCRIPTION REV	QUALITY SYMBOL ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE INCH		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY DATE		TITLE 120V 15A GFCI PLUG W/ 4 RCPT WEATHER RESIST BOX NEMA 5-15			
			4 PLACES	±---	±---	HRUIZ01	2013/02/08				
			3 PLACES	±---	±.005	CHECKED BY DATE		MOLEX MOLEX INCORPORATED			
			2 PLACES	±0.13	±.010	HKNEELAN	2014/07/22				
			1 PLACE	±0.25	±.020	APPROVED BY DATE					
	ANGULAR ±1/2°			JFMURPHY	2015/04/20	SHEET NO. 1 OF 1					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE TABLE								
A			SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

J
I
H
G
F
E
D
C
B
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301530085