

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301530146

Status:

Active

Overview:

Ground Fault Circuit Interrupter (GFCI) Products

Description:

Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, NEMA L6-20, 20A, 240V, 7.62m (25.0') Cord Length



Documents:	
Brochure (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR6837
UL	E66308
General	
Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 4
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Ground Fault Circuit Interrupter (GFCI) Products
Product Name	Safeway
Receptacle Type	N/A
Type	GFCI Commercial Duty, Single Phase
UPC	78678837418
Physical	
Cord Diameter	10.92mm (.430")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	7.62m (25.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	1
Packaging Type	Bag
Electrical	
Cord Type	12/3 SJTW
Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA L6-20
Voltage - Maximum	240V
Material Info	
Engineering Number	20054-25

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
130153 Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301530146