

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530155](#)
Status: **Active**
Overview: [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
Description: Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, NEMA L6-20 Plug & Connector, 20A, 240V, 0.61m (2.0') Cord Length

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family Power Distribution
Series [130153](#)
Enclosure Rating NEMA 4X
GFCI Reset Automatic
Mounting Style Portable
Open Neutral Relay Yes
Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
Product Name Super-Safeway
Receptacle Type N/A
Type GFCI Industrial Duty, Single Phase
UPC 78678888290

Physical

Cord Diameter 10.67mm (.420")
Cord Grip Body Size Internal Double C-Clamp
Cord Length 0.61m (2.0')
Feed-Thru Yes
Flip Lid No
Material - Housing Nylon
Number of Receptacles 1
Packaging Type Bag

Electrical

Cord Type 12/3 SJEOOW
Current - Maximum per Contact 20.0A
GFCI Yes-In-line
Ground Continuity Monitor No
NEMA Configuration NEMA L6-20
Voltage - Maximum 120V

Material Info

Engineering Number 24052-1A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

China RoHS

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130153](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301530155