

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301530181

Status:

Active

Overview:

Ground Fault Circuit Interrupter (GFCI) Products

Description:

Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, Flying Leads, 30A, 240V, 0.61m (2.0') Cord Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E66308
General	
Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 6P
GFCI Reset	Automatic
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Ground Fault Circuit Interrupter (GFCI) Products
Product Name	Super-Safeway
Receptacle Type	N/A
Type	GFCI Industrial Duty, Single Phase
UPC	78678888312
Physical	
Cord Diameter	13.00mm (.512")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Net Weight	0.855/kg
Number of Receptacles	0
Packaging Type	Bag
Electrical	
Cord Type	10/3 SJEOOW
Current - Maximum per Contact	30.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	N/A
Voltage - Maximum	240V
Material Info	
Engineering Number	30053-0A
Reference - Drawing Numbers	
Sales Drawing	SD-130153-035



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Relevant	
REACH SVHC	
Not Relevant	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130153 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301530181