

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301530242

Status:

Active

Overview:

Ground Fault Circuit Interrupter (GFCI) Products

Description:

Super-Safeway Fixed Mount Industrial GFCI, Permanent Mount, Multi Phase, Manual Reset, Flying Leads, 30A, 120/208V 3 Phase, 0.61m (2.0') Lead Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E66308
General	
Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 6P
GFCI Reset	Manual
Mounting Style	Permanent
Open Neutral Relay	Yes
Overview	Ground Fault Circuit Interrupter (GFCI) Products
Product Name	Super-Safeway
Receptacle Type	N/A
Type	GFCI Industrial Duty, Multi-Phase
UPC	78172542943
Physical	
Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	0.61m (2.0')
Feed-Thru	No
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	0
Packaging Type	Carton
Electrical	
Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	N/A
Voltage - Maximum	120V / 208V / 3 Phase
Material Info	
Engineering Number	30053-2M5F
Reference - Drawing Numbers	
Sales Drawing	SD-130153-039

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130153 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[130153-0242](#)