

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301540002

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Standard Molded W Cordset, 3 Pole/3 Wire SOOW Cordset, Cordset Length 0.91m (3.0'), Non-NEMA 15A/125V 10A/250V

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Wiring Devices
Series	130154
IP Rating	IP67
NEMA Configuration	Non-NEMA
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite
Receptacle Type	Triple
Specialty	N/A
Type	Molded W Cordset
UPC	78678808604
Physical	
Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Locking Blade	Yes
Poles	3-pole/3-wire
Electrical	
Cord Type	12/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V / 250V
Material Info	
Engineering Number	09589
Reference - Drawing Numbers	
Sales Drawing	1301540002-000



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130154 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301540002