

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301540040

Status:

Active

Overview:

Heavy-Duty Industrial Wiring Devices

Description:

Super-Safeway Inline GFCI Molded Y Cordset, 2 Pole/3 Wire SJOW Cordset, Cordset Length 0.91m (3.0'), NEMA 5-15, 125V



Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                      |
|-------------------------------|--------------------------------------|
| General                       |                                      |
| Product Family                | Wiring Devices                       |
| Series                        | 130154                               |
| IP Rating                     | N/A                                  |
| NEMA Configuration            | NEMA 5-15                            |
| Overview                      | Heavy-Duty Industrial Wiring Devices |
| Product Name                  | Super-Safeway                        |
| Receptacle Type               | Duplex                               |
| Specialty                     | N/A                                  |
| Type                          | Molded Y Cordset                     |
| UPC                           | 78678837379                          |
| Physical                      |                                      |
| Flange                        | No                                   |
| Flip Lid                      | No                                   |
| Gender                        | Male-Female                          |
| Length                        | 0.91m (3.0')                         |
| Locking Blade                 | No                                   |
| Poles                         | 2-pole/3-wire                        |
| Electrical                    |                                      |
| Cord Type                     | 12/3 SJOW                            |
| Current - Maximum per Contact | 15.0A                                |
| GFCI                          | Yes-In-line                          |
| Lighted Connector             | No                                   |
| Voltage - Maximum             | 125V                                 |
| Material Info                 |                                      |
| Engineering Number            | 1447-Y-IN                            |

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Reviewed                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Reviewed |
| ELV                                                           | Not Reviewed |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

130154 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301540040](#)