

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301550160

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Connector with California Style Locking Blade, 3 Pole/4 Wire, Non-NEMA, 50A/250V/3ø, Cord Grip Body Size F5



Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR6837
UL		E10176
General		
Product Family		Wiring Devices
Series		130155
IP Rating		IP67
NEMA Configuration		Non-NEMA Locking CA
Overview		Watertite Extreme Wet-Location Wiring Solutions
Product Name		Watertite Extreme
Receptacle Type		Single
Specialty		N/A
Type		Connector
UPC		78678801472
Physical		
Cord Grip Body Size		F5 1 1/4"
Flange		No
Flip Lid		No
Gender		Female
Length		N/A
Locking Blade		Yes
Net Weight		661.790/g
Poles		3-pole/4-wire
Electrical		
Cord Type		N/A
Current - Maximum per Contact		50.0A
GFCI		No
Lighted Connector		No
Voltage - Maximum		250V
Material Info		
Engineering Number		CS83W64

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130155 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301550160](#) [CS83W64](#)