

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301550167](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Plug with California Style Locking Blade, 2 Pole/3 Wire, Non-NEMA, 480V, Cord Grip Body Size F5

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E10176

General

Product Family Wiring Devices
Series [130155](#)
IP Rating IP67
NEMA Configuration Non-NEMA Locking CA
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
Product Name Watertite Extreme
Receptacle Type N/A
Specialty N/A
Type Plug
UPC 78678801456

Physical

Cord Grip Body Size F5 1 1/4"
Flange No
Flip Lid No
Gender Male
Length N/A
Locking Blade Yes
Poles 2-pole/3-wire

Electrical

Cord Type N/A
Current - Maximum per Contact 50.0A
GFCI No
Lighted Connector No
Voltage - Maximum 480V

Material Info

Engineering Number CS84W65



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130155](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301550167