

	10	9	8	7	6	5	4	3	2	1					
F											F				
E	BALANCER MODEL		LOAD CAPACITY CHART		CABLE TRAVEL (FOOT /METERS)		BALANCER OPTION: R = RATCHET LOCK BU = UPPER & LOWER BULLARD HOOKS BCU = BULLARD HOOKS & ADJUSTABLE CLAMPS S = CABLE TRAVEL = 1.5 M -SS = STAINLESS STEEL CABLE NC = NYLON COATED CABLE								
			WEIGHT RANGE FOR EACH BALANCER MODEL												
	MATERIAL NUMBER	MODEL NUMBER	LBS.	KGS.	FT.	M.									
	1301710300	25EB	18 - 25	8.2 - 11.4	6.6	2.0	STANDARD BALANCER								
	1301710301	25EBR	18 - 25	8.2 - 11.4	6.6	2.0	STANDARD BAL. W/ RATCHET LOCK								
	1301710311	25EBBU	18 - 25	8.2 - 11.4	6.6	2.0	BALANCER W/UPPER & LOWER BULLARD HOOKS								
1301710318	25EBRBU	18 - 25	8.2 - 11.4	6.6	2.0	BAL. W/UPPER & LOWER BULLARD HOOKS & RATCHET LOCK									
1301710319	25EBBCU	18 - 25	8.2 - 11.4	6.6	2.0	BAL. W/UPPER & LOWER BULLARD HOOKS & ADJ. CLAMPS									
1301710320	25EBNC	18 - 25	8.2 - 11.4	6.6	2.0	STANDARD BAL. W/ NYLON COATED CABLE									
D	1301710302	35EB	25 - 35	11.4 - 15.9	6.6	2.0	STANDARD BALANCER								
	1301710052	35EB-SS	25 - 35	11.4 - 15.9	6.6	2.0	STANDARD BALANCER W/ STAINLESS STEEL CABLE								
	1301710303	35EBR	25 - 35	11.4 - 15.9	6.6	2.0	BALANCER W/ RATCHET LOCK								
	1301710312	35EBBCU	25 - 35	11.4 - 15.9	6.6	2.0	BAL. W/UPPER & LOWER BULLARD HOOKS & ADJ. CLAMPS								
	1301710313	35EBBU	25 - 35	11.4 - 15.9	6.6	2.0	BAL. W/UPPER & LOWER BULLARD HOOKS								
	1301710314	35EBRBU	25 - 35	11.4 - 15.9	6.6	2.0	BAL. W/UPPER & LOWER BULLARD HOOKS & RATCHET LOCK								
	1301710321	35EBNC	25 - 35	11.4 - 15.9	6.6	2.0	STANDARD BALANCER W/ NYLON COATED CABLE								
	1301710304	35EBS	25 - 35	11.4 - 15.9	4.9	1.5	STANDARD BALANCER W/ CABLE TRAVEL 1.5 M								
	1301710305	45EB	35 - 45	15.9 - 20.5	6.6	2.0	STANDARD BALANCER								
1301710306	45EBR	35 - 45	15.9 - 20.5	6.6	2.0	BALANCER W/ RATCHET LOCK									
C	1301710315	45EBBU	35 - 45	15.9 - 20.5	6.6	2.0	BAL. W/UPPER & LOWER BULLARD HOOKS								
	1301710316	45EBRBU	35 - 45	15.9 - 20.5	6.6	2.0	BAL. W/UPPER & LOWER BULLARD HOOKS & RATCHET LOCK								
	1301710322	45EBNC	35 - 45	15.9 - 20.5	6.6	2.0	STANDARD BALANCER W/ NYLON COATED CABLE								
	1301710307	48EBS	35 - 48	15.9 - 21.8	4.9	1.5	STANDARD BALANCER W/ CABLE TRAVEL 1.5 M								
	1301710308	48EBSR	35 - 48	15.9 - 21.8	4.9	1.5	BALANCER W/ RATCHET LOCK & CABLE TRAVEL 1.5 M								
B	1301710309	60EBS	45 - 60	20.5 - 27.3	4.9	1.5	STANDARD BALANCER W/ CABLE TRAVEL 1.5 M								
	1301710310	60EBSR	45 - 60	20.5 - 27.3	4.9	1.5	BALANCER W/ RATCHET LOCK & CABLE TRAVEL 1.5 M								
	1301710317	60EBSBU	45 - 60	20.5 - 27.3	4.9	1.5	BAL. W/UPPER & LOWER BULLARD HOOKS & CABLE TRAVEL 1.5 M								
A	RELEASE TO SALES EC NO: IPG2017-0821 DRWN: VOU 2017/04/28 CHKD: BPATTERS 2017/04/28 APPR: JFMURPHY 2017/05/03				DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE INCH / MM		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
								mm	INCH	DRAWN BY DATE		EB BALANCER ----- -----			
							4 PLACES	±---	±---	MCHOJECK 2012/07/24					
							3 PLACES	±---	±.005	CHECKED BY DATE					
							2 PLACES	±0.13	±.010	BPATTERS 2017/04/28					
							1 PLACE	±0.25	±.020	APPROVED BY DATE					
							ANGULAR ±.5°			JFMURPHY 2017/05/03		MOLEX INCORPORATED			
							DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.					
										SEE TABLE		DOCUMENT NO.			SHEET NO.
										SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
	10	9	8	7	6	5	4	3	2	1					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301710319](#)