

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1302100066](#)
Status: **Active**
Description: Micro-Change Stranded Cable, Shielded PVC, ITC/PLTC Type, 22 AWG, 4 Conductors, 76.20m Length, Black

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable
Series	130210
Crimp Quality Equipment	Yes
Product Name	Micro-Change (M12)
UPC	78678834515
Physical	
Cable Length	76.20m
Circuits (Loaded)	4
Color - Cable Jacket	Black
Material - Outer Jacket	PVC
Net Weight	27.215/g
Outer Jacket Diameter	7.11mm
Packaging Type	Carton
Temperature Range - Operating	-20° to +105°C
Wire Size AWG	22
Wire/Cable Type	Shielded PVC
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	300V
Material Info	
Engineering Number	85-2294M



EU ELV Compliant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Not Low-Halogen	China RoHS
For more information, please visit Contact US	
China ROHS ELV RoHS Phthalates	Green Image Compliant Not Contained

Search Parts in this Series
[130210](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1302100066](#)