

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1302261797

Status:

Active

Description:

Heavy Duty Stranded Cable, Type SOW/SOOW, 16 AWG, 2 Conductors, 304.80mm Length, Black

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable
Series	130226
Crimp Quality Equipment	Yes
Product Name	Heavy Duty
UPC	78678864168
Physical	
Cable Length	304.80mm (1.0')
Circuits (Loaded)	2
Color - Cable Jacket	Black
Net Weight	5.080/kg
Outer Jacket Diameter	9.40mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +90°C
Wire Size AWG	16
Wire/Cable Type	SOOW, SOW
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	R62110113

Image coming soon

Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130226 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1302261797