

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1302430021](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Haztex Wide Area LED Work Light, 4 x 20W, Plug 14/3 SOOW 7.62m (25.0')

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130243
Comments	Class 1, Division 2, Groups B, C, and D, Class 1, Division 2, Groups B, C, and D
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 3R
Outlet	None
Overview	Wide-Area Lighting Products
Product Name	Haztex
Type	Wide Area Lamps
UPC	78172536905

Physical

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	176.90m (6.960")
Duty	Hazardous
Guard Included	No
Guard Type	N/A
Height	166.50mm (6.555")
Length	706.37mm (27.810")
Material - Globe	Clear Polycarbonate
Material - Guard	Silicone Rubber
Mounting Style	Variable
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	LED
Cord Type - Primary	14/3 SOOW
Lamp Type	20W LED
Lamp Wattage - Maximum	20W x 4
Lumens	5270
On/Off Switch	No
Voltage (Fixture) - Maximum	120V, 277V

Material Info

Engineering Number	1076HZ25025143
--------------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130243](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1302430021