

6


5

4


3

2

1

MALE INSERT  
FACE VIEW

1 DRAIN WIRE  
2 WHITE<DB>  
3 YELLOW<DG>  
4 BLUE <DA>



CC03A-J30-M020

Wire type  
20/3C AWG Brown  
PVC

cable length  
M020----2 Meter  
M100-----10 Meter

## MECHANICAL

CONTACT: GOLD/NICKEL OVER COPPER ALLOY


INSERT : NYLON 6/6

COUPLING NUT: ZINC DIECAST WITH BLACK EPOXY COATED

MOLDED BODY: GREY PVC

CABLE COLOR: BROWN

CABLE MARKING: FANC-110SBH KURAMO FA(JAPANESE WORDS)

CC-LINK Ver.1.10 KURAMO E162205-K c  us AWM Style 2464

I A 80C 300V VW-1 FT1 LF

## ELECTRICAL

VOLTAGE RATING: 250V AC/DC

AMPERAGE: 4A

## ENVIRONMENTAL

PROTECTION: IP67 PER IEC 60529

IP68 PER SPEC PS-120001-001

OPERATION TEMP: 0°C~80°C

CABLE MARKING UPDATE  
EC NO: IGC2015-1192  
DRWN: CAVILLES 2014/12/30  
CHKD: TWOLDEGE  
APPR: JFMURPHY 2012/11/01

B

QUALITY  
SYMBOLS  
▽=0  
▽C=0

GENERAL TOLERANCES  
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±.005
2 PLACES	±.13	±.010
1 PLACE	±.25	±.020

ANGULAR ±.5°

DRAFT WHERE APPLICABLE  
MUST REMAIN  
WITHIN DIMENSIONS

DIMENSION STYLE  
INCH/MM

DRAWN BY DATE  
TWOLDEGE 2012/09/25  
CHECKED BY DATE  
VOU ---  
APPROVED BY DATE  
JFMURPHY 2012/11/01  
MATERIAL NO.

SCALE  
1:1DESIGN UNITS  
INCH THIRD ANGLE  
PROJECTION

TITLE  
CC-LINK MICRO CHANGE  
4-POLE MALE 90D  
20/3C SHLDED BROWN PVC

 MOLEX INCORPORATED

DOCUMENT NO.  
SD-130257-003

SHEET NO.  
1 OF 1

SIZE  
A

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX  
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

6

5

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1302570015](#) [1302570039](#) [1302570012](#) [1302570031](#) [1302570010](#)