

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1501761011](#)
Status: **Active**
Overview:
Description: Standard .062"+ Plug Housing, Single Row, without Panel Mount Latch, 1 Circuit

Agency Certification

UL E29179

General

Product Family Crimp Housings
Series [150176](#)
Application Power, Wire-to-Wire
Overview standard_062
Product Name Standard .062"+
UPC 889056490290

Physical

Circuits (maximum) 1
Color - Resin Natural
Flammability 94V-2
Gender Plug
Glow-Wire Capable No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 0.370/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.68mm
Pitch - Termination Interface 3.68mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification 1501760001-AS-000
Packaging Specification PK-150176-001-001
Product Specification 1501760001-PS-000
Sales Drawing SD-150176-001-000
Test Summary 1501760001-TS-000

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Compliant
RoHS Phthalates Not Contained

Search Parts in this Series
[150176](#) Series

Mates With
Standard .062"+ Receptacle Housing
[150178](#)

Use With
Standard .062"+ Male Terminal [150180](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

150176-1011