

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1553111010](#)
Status: **Active**
Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)
Description: Flamar Power Cable, PVC Jacket, Braided Shielding Overall, 6 Circuits, 4x(6.00mm²) with Green-Yellow Ground + (2x1.50mm² with Braided Shield) / 4x(10 AWG) with Green-Yellow Ground + (2x16 AWG with Braided Shield), 16.20mm (.244") Diameter, 100.0m (328.08') Length, Orange

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	155311
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Servo Motor
UPC	889056459761

Physical

Bending Radius - Minimum	> 15xOD
Cable Length	100.0m
Circuits (Loaded)	6 (4+2)
Color - Cable Jacket	Orange
Insulation	TPE
Material - Outer Jacket	PVC
Net Weight	0.010/g
Outer Jacket Diameter	16.20mm
Packaging Type	Reel
Temperature Range - Operating	+5° to +80°C
Wire Size AWG	10, 16
Wire Size mm ²	1.50, 6.00
Wire/Cable Type	UL AWM 2570 / CSA

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	1000V

Material Info

Engineering Number	1X100M
--------------------	--------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[155311](#) Series

Use With

Brad M23 [120230](#) , [120233](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155311-1010](#)