

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1553210004](#)
Status: **Active**
Overview:
Description: Flamar Power Cable, WSOR Jacket, Braided Shielding Overall, 4 Circuits, 2.50mm² with Green-Yellow Ground / 14 AWG with Green-Yellow Ground, 10.60mm (.417") Diameter, 100.0m (328.08') Length, Orange

Agency Certification

UL E172949

General

Product Family Cable
Series [155321](#)
Crimp Quality Equipment Yes
Geographic Area Global
Overview flamar_standard_industrial_cables
Product Name Flamar, Servo Motor
UPC 889056460361

Physical

Bending Radius - Minimum > 10xOD
Cable Length 100.0m
Circuits (Loaded) 4
Color - Cable Jacket Orange
Insulation TPE
Material - Outer Jacket WSOR
Net Weight 0.194/kg
Outer Jacket Diameter 10.60mm
Packaging Type Reel
Temperature Range - Operating -25° to +80°C
Wire Size AWG 14
Wire Size mm² 2.50
Wire/Cable Type UL AWM 21939 / CSA

Electrical

Current - Maximum per Contact Contact Molex
Voltage - Maximum 1000V

Material Info

Engineering Number 1X100M

Reference - Drawing Numbers

Product Specification 1553210001-P1E

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[155321](#) Series

Use With

Brad M23 [120230](#) , [120233](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

155321-0004