

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1553310003](#)
Status: **Active**
Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)
Description: Flamar Power Cable, PUR Jacket, Braided Shielding Overall, 4 Circuits, 1.50mm² with Green-Yellow Ground / 16 AWG with Green-Yellow Ground, 9.00mm (.354") Diameter, 1000.0m (3280.83') Length, Orange

Documents:

[Product Specification 1553310001-P1E \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

UL E172949

General

Product Family Cable
Series [155331](#)
Crimp Quality Equipment Yes
Geographic Area Global
Overview [Flamar Standard and Custom Cables for Industrial Automation](#)
Product Name Flamar, Servo Motor
UPC 889056461337

Physical

Bending Radius - Minimum > 10xOD
Cable Length 1000.0m
Circuits (Loaded) 4
Color - Cable Jacket Orange
Insulation TPE
Material - Outer Jacket PUR
Net Weight 0.127/kg
Outer Jacket Diameter 9.00mm
Packaging Type Reel
Temperature Range - Operating -40° to +80°C
Wire Size AWG 16
Wire Size mm² 1.50
Wire/Cable Type UL AWM 21223 / CSA

Electrical

Current - Maximum per Contact Contact Molex
Voltage - Maximum 1000V

Material Info

Engineering Number 1X1000M

Reference - Drawing Numbers

Product Specification 1553310001-P1E



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[155331](#) Series

Use With

Brad M23 [120230](#) , [120233](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155331-0003](#)