

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1554215001](#)
Status: **Active**
Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)
Description: Flamar PROFINET* C Network Cable, WSOR Jacket, Braided Shielding Overall, 4 Circuits, 2x(2x0.34mm²) / 2x(2x22 AWG), 6.80mm (.268") Diameter, 300.0m (984.25') Length, Green

Documents:

[Test Summary 1202098313-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

UL E172949

General

Product Family Cable
Series [155421](#)
Comments 3 reels of 100.0m each
Crimp Quality Equipment Yes
Geographic Area Global
Overview [Flamar Standard and Custom Cables for Industrial Automation](#)
Product Name Flamar, Network
Protocol PROFINET
UPC 889056464758

Physical

Bending Radius - Minimum > 15xOD
Cable Length 300.0m
Circuits (Loaded) 4
Color - Cable Jacket Green
Insulation PE
Material - Outer Jacket WSOR
Net Weight 0.070/kg
Outer Jacket Diameter 6.80mm
Packaging Type Reel
Temperature Range - Operating -10° to +60°C
Wire Size AWG 22
Wire Size mm² 0.34
Wire/Cable Type UL AWM 21215 / CSA

Electrical

Current - Maximum per Contact Contact Molex
Voltage - Maximum 600V

Material Info

Engineering Number CAB-12-3X100M

Reference - Drawing Numbers

Test Summary 1202098313-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[155421](#) Series

Use With

Micro-Change (M12) [130047](#) , [120100](#) ,
[130034](#) , [120071](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[155421-5001 \(5 Meters\)](#) [155421-5001 \(15 Meters\)](#)