

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1714003020](#)
Status: **Active**
Overview: [Impel and Impel Plus Backplane Solutions](#)
Description: Impel 90 Ohm, 6 Pair Right-Angle Daughtercard, 1.90mm Pitch, Left Guided, 10 Columns, 120 Circuits, Plated Through Hole Dimension 0.36mm

Documents:

3D Model	Application Specification AS-171320-991-001 (PDF)
3D Model (PDF)	Application Specification AS-171320-992-001 (PDF)
Drawing (PDF)	Packaging Specification PK-78888-088-001 (PDF)
Product Specification PS-171320-999-001 (PDF)	Symbol Footprint Data SYM-171400-3020-001 (PDF)
Application Specification AS-171320-990-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family	Backplane Connectors
Series	171400
Application	Coplanar, Daughtercard
Application Tooling Documents	TM-622018899-001
Component Type	PCB Receptacle
Overview	Impel and Impel Plus Backplane Solutions
Product Name	Impel
UPC	887191117591

Physical

Circuits (Loaded)	120
Circuits (maximum)	120
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Nickel, Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	54.836/g
Number of Columns	10
Number of Pairs	6
Number of Rows	12
Orientation	Right Angle
PC Tail Length	1.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Packaging Type	Tray
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Temperature Range - Operating	-55° to +85°C

Electrical

Current - Maximum per Contact	0.75A
Data Rate	40.0 Gbps
Impedance	90Ω



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[171400 Series](#)

Mates With

Impel Vertical Backplane Header
[1713953107](#)

Shield Type	Full Shield
Voltage - Maximum	29.9V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-171320-990-001, AS-171320-991-001, AS-171320-992-001
Electrical Model Document	1714002001A-000, 1714002002-000
Packaging Specification	PK-78888-088-001
Product Specification	PS-171320-999-001
S-Parameter Model	1714002001-SP-000, 1714002002-000
Sales Drawing	SD-171400-0002-001
Symbol/Footprint Data	SYM-171400-3020-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

171400-3020