

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1714461114](#)
Status: **Active**
Overview: [SpeedMezz Connector Family](#)
Description: SpeedStack Vertical Plug, 0.80mm Pitch, 1.90mm Height, 60 Circuits, UL94V-0, Black

Documents:
[3D Model](#) [Packaging Specification PK-70873-6003-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[3D Model \(PDF\)](#)


General
Product Family PCB Headers
Series [171446](#)
Application Board-to-Board
Overview [SpeedMezz Connector Family](#)
Product Name SpeedStack
UPC 889056432757

Physical
Breakaway No
Circuits (Loaded) 60
Circuits (maximum) 60
Color - Resin Black
Durability (mating cycles max) 20
Glow-Wire Capable No
Material - Metal Copper Alloy
Material - Plating Mating Gold
Material - Plating Termination Matte Tin
Material - Resin Liquid Crystal Polymer
Net Weight 0.526/g
Number of Rows 2
Orientation Vertical
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 0.80mm
Pitch - Termination Interface 0.80mm
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -40° to +105°C
Termination Interface: Style Surface Mount

Electrical
Current - Maximum per Contact 0.8A
Voltage - Maximum 5V AC (RMS)/DC

Material Info

Reference - Drawing Numbers
[Packaging Specification](#) PK-70873-6003-001
[Sales Drawing](#) SD-171446-1000-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[171446 Series](#)

Mates With
SpeedStack Vertical Receptacle [171450](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

171446-1114