

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1722533112](#)
Status: **Active**
Overview: [Ultra-Fit Power Connectors](#)
Description: Ultra-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 20-22 AWG
Replacement Part Number : <http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=17225361121722536112>

Documents:

Drawing (PDF)	Application Specification AS-172323-0001 (PDF)
Product Specification 1723230001-TS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-172323-0001-001 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Terminals
Series	172253
Application	Power, Wire-to-Board
Comments	See Product Specification for maximum current rating by circuit size and wire AWG, See Product Specification for maximum current rating by circuit size and wire AWG
Crimp Quality Equipment	Yes
Overview	Ultra-Fit Power Connectors
Product Name	Ultra-Fit
Replacement Part Number	1722536112
UPC	887191723808

Physical

Durability (mating cycles max)	200
Gender	Female
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin over Nickel
Net Weight	0.144/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	1.524µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-1.50mm
Wire Size AWG	20, 22
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	12.0A
Voltage - Maximum	400V AC (RMS)/DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-172323-0001
Application Tooling Documents	ATS-639041600-001
Product Specification	1723230001-TS-000, PS-172323-0001-001
Sales Drawing	SD-172253-1000-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[172253](#) Series

Use With

Ultra-Fit Single Row Receptacle Housing
[1722561102](#) , [1722561103](#) , [1722561104](#)
 , [1722561105](#) , [1722561106](#) , [1722561107](#)
 , [1722561108](#) , [1722562102](#) , [1722562103](#)
 , [1722562104](#) , [1722562105](#) , [1722562106](#)
 , [1722562107](#) , [1722562108](#)
Ultra-Fit
Dual Row Receptacle Housing [1722581104](#)
 , [1722581106](#) , [1722581108](#) , [1722581110](#)
 , [1722581112](#) , [1722581114](#) , [1722581116](#)
 , [1722582104](#) , [1722582106](#) , [1722582108](#)
 , [1722582110](#) , [1722582112](#) , [1722582114](#) ,
[1722582116](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool	<u>11030016</u>
Hand Crimp Tool	<u>638275400</u>
for Ultra-Fit Crimp	
Terminals, 20-22	
AWG (UL1061) wires	

This document was generated on 01/09/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[172253-3112](#) [172253-3112 \(Loose Piece\)](#) [172253-3112 \(Cut Strip\)](#) [172253-3112 \(Mouser Reel\)](#)