

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1726732003

Status:


Active

Overview:

Super Sabre Connector System

Description:

7.50mm Pitch Super Sabre Plug Crimp Housing, UL 94V-0, 3 Circuits



Documents:	
3D Model (PDF)	Packaging Specification PK-43680-001-001 (PDF)
3D Model	Test Summary TS-171825-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-171825-001-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	172673
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	Super Sabre Connector System
Product Name	Super Sabre
UPC	889056025973
Physical	
Circuits (maximum)	3
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.621/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	7.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	34.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-43680-001-001
Product Specification	PS-171825-001-001
Sales Drawing	SD-172673-001-001
Test Summary	TS-171825-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

172673 Series

Mates With

172672 Super Sabre Receptacle Crimp Housing

Use With

171826 Super Sabre Male Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[172673-2003](#)