


10	9	8	7	6	5	4	3	2	1
MATERIAL NO. LOOSE PIECE	ENG. NO.	MATERIAL NO. TAPE MOUNTED	ENG. NO. TAPE MOUNTED	STUD SIZE	"S" ±.003 (0.08)	"W" MAX	"C" MIN	"L" MAX	"H" ±.020 (0.51)
190440137	B-101-12HD	190440138	B-101-12HDT	12	.515 (13.10)	.760 (19.30)	.611 (15.52)	1.280 (32.51)	1.556 (39.52)
190440139	B-101-14HD	-----	-----	14	.265 (6.73)				
190440140	B-101-38HD	-----	-----	38	.390 (9.91)				
190440141	B-101-56HD	-----	-----	56	.328 (8.33)				
190440142	B-101-76HD	190440229	B-101-76HDT	76	.453 (11.51)				
190440161	B-128-06HD	-----	-----	6	.146 (3.71)	.385 (9.78)	.303 (7.70)	.785 (19.94)	1.234 (31.34)
190440162	B-128-08HD	-----	-----	8	.173 (4.39)				
190440163	B-128-10HD	190440164	B-128-10HDT	10	.198 (5.03)				
190440166	B-130-10HD	190440022	B-130-10HDT	10	.198 (5.03)	.540 (13.72)	.393 (9.98)	.952 (24.18)	
190440167	B-130-14HD	190440023	B-130-14HDT	14	.265 (6.73)				
190440168	B-130-56HD	190440024	B-130-56HDT	56	.328 (8.33)				
190440172	B-136-04HD	-----	-----	4	.119 (3.02)	.292 (7.42)	.303 (7.70)	.741 (18.82)	
190440173	B-136-06HD	190440026	B-136-06HDT	6	.146 (3.71)				
190440174	B-136-08HD	190440027	B-136-08HDT	8	.173 (4.39)				
190440180	B-140-10HD	-----	-----	10	.198 (5.03)	.598 (15.19)	.475 (12.07)	1.056 (26.82)	1.426 (36.22)
190440182	B-140-14HD	190440183	B-140-14HDT	14	.265 (6.73)				
190440184	B-140-38HD	190440185	B-140-38HDT	38	.390 (9.91)				
190440186	B-140-56HD	190440187	B-140-56HDT	56	.328 (8.33)				



NOTE(S):
1. MATERIAL: COPPER .050" (1.27 THK)
2. PLATING: ELECTROPLATE TIN.
WIRE SIZE: 16-14 AWG
1.0 - 2.5 MM²

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
A/ = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: MIGR & UPDATE DIM					molex				
	IN/MM		NTS											
E/ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 613281 DRWN: DMYRICK 2019/03/05 CHK'D: JMACNEIL 2019/03/08 APPR: JMACNEIL 2019/03/08					RING TONGUE TERMINAL HEAVY-DUTY KRIMPTITE 16-14 AWG				
F/ = 0														
S/ = 0	4 PLACES ±		±		INITIAL REVISION: DRWN: DMYRICK 2004/05/07 APPR: RDEROSS 2004/05/07					DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
▼ = 0	3 PLACES ±		± 0.005							SD-19044-008		PSD	001	A1
▽ = 0	2 PLACES ±		± 0.13 ± 0.01		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER					
□ = 0	1 PLACE ±		± 0.25 ±		SEE CHART		GENERAL MARKET		1 OF 1					
■ = 0	0 PLACES ±		±											
⊠ = 0	ANGULAR TOL ± 0.5 °				THIRD ANGLE PROJECTION		DRAWING	SERIES						
▽ = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				B-SIZE		19044							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19044-0338