

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2016060690

Status:

Active

Overview:

High-Current, Universal-Clamp Terminal Blocks

Description:

High Current Universal Clamp Tapping Terminal Block, Screw Mount, 380.0A / 600V, Grey Housing and Cover, 1 Circuit, 4 Terminations

Documents:

- 3D Model

RoHS Certificate of Compliance (PDF)
- Drawing (PDF)

Product Literature (PDF)
- 3D Model (PDF)

Agency Certification

UL

E48521

General

Product Family

Terminal Blocks

Series

201606

Application

Wire-to-Wire

Component Type

One Piece

Overview

High-Current, Universal-Clamp Terminal Blocks

Product Name

Universal Clamp

Type

Universal Clamp

UPC

78172551156

Physical

Circuits (Loaded)

1

Circuits (maximum)

1

Color - Resin

Grey

Entry Angle

Horizontal

Lock to Mating Part

None

Material - Metal

Aluminum

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Polyamide

Number of Rows

2

Orientation

Vertical

Panel Mount

Screws

Pitch - Mating Interface

N/A

Polarized to Mating Part

N/A

Stackable

No

Temperature Range - Operating

-40° to +105°C

Termination Interface: Style

Screw

Wire Size AWG

2(2/0-2), 3(1/0-2), 500 MCM-3/0

Wire Size mm²

2(33.60-67.00), 3(33.60-53.00), 85.00-253.35

Electrical

Current - Maximum per Contact

380.0A

Voltage - Maximum

600V

Material Info

Engineering Number

MX-KE69

Reference - Drawing Numbers

Sales Drawing

2016060690-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

201606 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[201606-0690](#)