

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2016061625](#)
Status: **Active**
Overview: [High-Current, Universal-Clamp Terminal Blocks](#)
Description: High Current Universal Clamp Terminal Block, 35.00mm DIN-rail or Screw Mount, 230.0A / 1000V, Grey Housing, Red Cover, 1 Circuit

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E48521

General

Product Family Terminal Blocks
Series [201606](#)
Application Wire-to-Wire
Component Type One Piece
Overview [High-Current, Universal-Clamp Terminal Blocks](#)
Product Name Universal Clamp
Type Universal Clamp
UPC 78172551175

Physical

Circuits (Loaded) 1
Circuits (maximum) 1
Color - Resin Grey, Red
Entry Angle Horizontal
Lock to Mating Part None
Material - Metal Aluminum
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Polyamide
Number of Rows 1
Orientation Vertical
Panel Mount Screws
Pitch - Mating Interface N/A
Polarized to Mating Part N/A
Stackable No
Temperature Range - Operating -40° to +125°C
Termination Interface: Style Screw
Wire Size AWG 2(2-6), 4/0-4, 6+6+6
Wire Size mm² 13.30+13.30+13.30, 2(13.30-33.60), 21.00-107.00

Electrical

Current - Maximum per Contact 230.0A
Voltage - Maximum 1000V

Material Info

Engineering Number MX-KE162.4

Reference - Drawing Numbers

Sales Drawing 2016061620-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[201606](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[201606-1625](#)