


END LATCH LEVER OPTION



OVER-THE-TOP LEVER OPTION

OUTER SHROUD PART NUMBER	KEY OPTION
34745-0501	1
34745-0502	2
34745-0503	3
34745-0504	4
34745-0505	5
34745-0595	NIL

UNCHECKED cavity number(s) are OPEN																				
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15		76	77	78	79	80
☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐		☐	☐	☐	☐	☐
16	17	18	19	20	21	22	23	24	25	26	27	28	29	30		81	82	83	84	85
☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐		☐	☐	☐	☐	☐
31	32	33	34	35	36	37	38	39	40	41	42	43	44	45						
☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐						
46	47	48	49	50	51	52	53	54	55	56	57	58	59	60		86	87	88	89	90
☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐		☐	☐	☐	☐	☐
61	62	63	64	65	66	67	68	69	70	71	72	73	74	75		91	92	93	94	95
☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐		☐	☐	☐	☐	☐

FOR ADDITIONAL INFORMATION SEE E-34745-001

CUSTOMER PART NUMBER	ASSEMBLY PART NUMBER	LEVER PART NUMBER	LEVER OPTION	KEY OPTION	OUTER SHROUD PART NUMBER	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION															
CU5T-14A464-CD-000	34745-0001	34745-0801	END LATCH	1	34745-0501																
CU5T-14A464-CD-001	34745-0001	34745-0801	END LATCH	1	34745-0501																
CU5T-14A464-FD-000	34745-1001	34745-0802	TOP LATCH	1	34745-0501																
CU5T-14A464-FD-001	34745-1001	34745-0802	TOP LATCH	1	34745-0501																
CU5T-14A464-FD-002	34745-1002	34745-0802	TOP LATCH	1	34745-0501				4	5	6									76	
									19		21		23	24	25					81	
												37	38	39	40	41					
																56					
																71			74		



GPCM 95-WAY RECEPTACLE ASSY SEALED PIN OUT SHEET

CUSTOMER PART NUMBER	ASSEMBLY PART NUMBER	LEVER PART NUMBER	LEVER OPTION	KEY OPTION	OUTER SHROUD PART NUMBER	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION																							
CU5T-14A464-CD-002	34745-0002	34745-0801	END LATCH	1	34745-0501				4	5	6												76			79			
									19		21		23	24	25										81				
												37	38	39	40	41													
																56													
																71				74									
CU5T-14A464-CD-003	34745-0003	34745-0801	END LATCH	1	34745-0501				4	5	6												76			79			
											21		23	24	25										81				
												37	38	39	40	41													
																56													
																71				74									
CU5T-14A464-CD-004	34745-0004	34745-0801	END LATCH	1	34745-0501				4	5	6								13				76			79			
											21		23	24	25										81				
												37	38	39	40	41													
																56													
																71				74									
CU5T-14A464-CD-005	34745-0005	34745-0801	END LATCH	1	34745-0501				4	5									13		15		76			79			
							17	18	19		21		23	24	25	26								81					
									34	35			38	39	40	41													
							47								55	56		58									89	90	
						61	62							69	70	71		73	74								94	95	
CU5T-14A464-FD-003	34745-1003	34745-0802	TOP LATCH	1	34745-0501	1	2	3	4	5	6	7	8	9	10								76	77	78	79	80		
						16	17	18		20					25	26	27	28	29	30				81	82	83	84	85	
						31			34	35						41	42	43	44										
						46	47	48	49																		87		90
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75							92	93	94
CU5T-14A464-FD-004	34745-1004	34745-0802	TOP LATCH	1	34745-0501				4	5									13		15		76						
									19		21		23	24	25	26													
									34	35			38	39	40	41													
						46	47								55	56		58									89	90	
						61	62							69	70	71		73	74								94	95	
CU5T-14A464-FD-005	34745-1005	34745-0802	TOP LATCH	1	34745-0501				4	5									13				76						
							17	18	19		21		23	24	25	26													
									34	35			38	39	40	41													
							47								55	56		58									89	90	
						61	62							69	70	71		73	74								94	95	
CU5T-14A464-FD-006	34745-1006	34745-0802	TOP LATCH	1	34745-0501				4	5									13		15		76						
							17	18	19		21		23	24	25	26													
									34	35			38	39	40	41													
							47								55	56		58									89	90	
						61	62							69	70	71		73	74								94	95	
CU5T-14A464-CD-006	34745-0006	34745-0801	END LATCH	1	34745-0501	1	2	3				7	8	9	10								76	77	78	79	80		
						16	17	18		20						25	26	27	28	29	30		81	82	83	84	85		
						31			34	35							41	42	43	44									
						46	47	48	49																				
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75									



GPCM 95-WAY RECEPTACLE ASSY SEALED PIN OUT SHEET

CUSTOMER PART NUMBER	ASSEMBLY PART NUMBER	LEVER PART NUMBER	LEVER OPTION	KEY OPTION	OUTER SHROUD PART NUMBER	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION																							
CU5T-14A464-FD-007	34745-1007	34745-0802	TOP LATCH	1	34745-0501				4	5								13		15			76			79			
									19				23	24	25	26						81							
									34	35			38	39	40	41													
						46	47							55	56		58										89	90	
						61	62							69	70	71		73	74								94	95	
CU5T-14A464-FD-008	34745-1008	34745-0802	TOP LATCH	1	34745-0501				4				8	9		11	12	13	14	15			76	77			80		
							17				21			24			27	28	29	30						85			
							32								41		43	44	45										
															56														
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75					88		90		
CU5T-14A464-CD-007	34745-0007	34745-0801	END LATCH	1	34745-0501				4	5	6				10			13					76			79			
							17				21		23	24	25					29						81			
											35																		
														54	55	56													
														69	70	71				74									
CU5T-14A464-CD-008	34745-0008	34745-0801	END LATCH	1	34745-0501					19							11	12	13				76				80		
																	27	28								85			
								33				37	38						43	44	45								
																	57	58	59	60					87	88			
						61	62	63	64																			95	
CU5T-14A464-FD-009	34745-1009	34745-0802	TOP LATCH	1	34745-0501				4	5											15			76					
							17	18			21			24	25	26													
													38	39	40	41													
						46	47								55	56		58								89	90		
						61	62							69	70	71		73	74							94	95		
CU5T-14A464-FD-010	34745-1010	34745-0802	TOP LATCH	1	34745-0501				4	5											15			76					
							17	18			21			24	25	26													
											35		38	39	40	41													
						46	47								55	56		58								89	90		
						61	62							69	70	71		73	74							94	95		
CU5T-14A464-CD-009	34745-0009	34745-0801	END LATCH	1	34745-0501				4	5	6								13					76			79		
									19		21		23	24	25											81			
												37	38	39	40	41													
															55	56													
														69		71				74									
CU5T-14A464-FD-011	34745-1011	34745-0802	TOP LATCH	1	34745-0501				4	5	6								13					76			79		
									19		21		23	24	25											81			
												37	38	39	40	41													
															55	56													
														69		71				74									
CU5T-14A464-CD-010	34745-0010	34745-0801	END LATCH	1	34745-0501				4	5									13					76					
									19		21		23	24	25														
													38	39	40	41													
															55	56													
														69		71				74									



GPCM 95-WAY RECEPTACLE ASSY SEALED PIN OUT SHEET

CUSTOMER PART NUMBER	ASSEMBLY PART NUMBER	LEVER PART NUMBER	LEVER OPTION	KEY OPTION	OUTER SHROUD PART NUMBER	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION																								
CU5T-14A464-CD-011	34745-0011	34745-0801	END LATCH	1	34745-0501				4	5	6				10			13					76			79				
									19		21		23	24	25										81					
																	55	56												
																69		71				74								
CU5T-14A464-CD-012	34745-0012	34745-0801	END LATCH	1	34745-0501				4	5								13		15			76			79				
									19				23	24	25	26									81					
									34	35			38	39	40	41														
						46	47								55	56		58												
						61	62							69	70	71		73	74											
CU5T-14A464-CD-013	34745-0013	34745-0801	END LATCH	1	34745-0501	1	2	3				7	8	9	10							76	77	78	79	80				
						16	17	18		20					25	26	27	28	29	30		81	82	83	84	85				
						31			34	35						41	42	43	44											
						46	47	48	49																					
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75										
N/A	34745-1012	34745-0802	TOP LATCH	1	34745-0501			3						9			12	13	14	15										
								18						24			27													
						31	32			35																				
						46	47	48						54		56														
						61			64						70	71	72	73	74	75										
N/A	34745-1013	34745-0802	TOP LATCH	1	34745-0501			3						9			12	13	14	15										
								18						24			27													
						31	32			35																				
						46								54																
						61			64						70	71	72	73	74	75										
N/A	34745-1014	34745-0802	TOP LATCH	1	34745-0501			3						9			12	13	14											
								18						24																
						31	32																							
						46	47	48								56														
						61			64						70	71														
N/A	34745-1015	34745-0802	TOP LATCH	1	34745-0501			3						9			12	13	14											
								18						24																
						31	32																							
						46																								
						61			64							70	71													
CU5T-14A464-FD-012	34745-1016	34745-0802	TOP LATCH	1	34745-0501				4	5								13		15			76							
									19		21		23	24	25	26														
									34	35			38	39	40	41														
							47								55	56		58												
						61	62							69	70	71		73	74											
CU5T-14A464-FD-013	34745-1017	34745-0802	TOP LATCH	1	34745-0501				4	5								13		15			76				80			
									19		21		23	24	25	26											85			
									34	35			38	39	40	41														
							47								55	56		58												
						61	62								69	70	71		73	74										



GPCM 95-WAY RECEPTACLE ASSY SEALED PIN OUT SHEET

CUSTOMER PART NUMBER	ASSEMBLY PART NUMBER	LEVER PART NUMBER	LEVER OPTION	KEY OPTION	OUTER SHROUD PART NUMBER	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION																								
CU5T-14A464-FD-014	34745-1018	34745-0802	TOP LATCH	1	34745-0501				4	5								13		15		76				80				
									19		21		23	24	25	26														
									34	35			38	39	40	41														
							47								55	56		58									89	90		
						61	62							69	70	71		73	74								94	95		
CU5T-14A464-CD-014	34745-0014	34745-0801	END LATCH	1	34745-0501				4	5								13		15		76			79					
									19				23	24	25	26									81					
									34	35			38	39	40	41														
							47								55	56		58									89	90		
						61	62							69	70	71		73	74								94	95		
CU5T-14A464-CD-015	34745-0015	34745-0801	END LATCH	1	34745-0501				4	5								13		15		76			79					
							17	18	19		21		23	24	25	26									81					
										35			38	39	40	41														
							47								55	56		58									89	90		
						61	62							69	70	71		73	74								94	95		
CU5T-14A464-FD-015	34745-1019	34745-0802	TOP LATCH	1	34745-0501			3						9			12	13	14	15				78						
								18					24			27										83				
						31	32			35																				
						46	47	48					54		56												87	88		
						61			64						70	71	72	73	74	75								95		
CU5T-14A464-CD-016	34745-0016	34745-0801	END LATCH	1	34745-0501				4									13		15		76			79					
							17	18	19		21		23	24	25	26									81					
										35			38	39	40	41														
							47								55	56		58									89	90		
						61	62							69	70	71		73	74								93	94	95	
CU5T-14A464-CD-017	34745-0017	34745-0801	END LATCH	1	34745-0501		2		4						10			13		15		76			79	80				
							17	18	19		21		23	24	25	26	27			30				81						
										35			38	39	40	41			44	45										
							47								55	56		58	59	60							89	90		
						61	62					67		69	70	71		73	74	75							94	95		
CU5T-14A464-CD-018	34745-0018	34745-0801	END LATCH	1	34745-0501		2		4					9	10			13		15		76			79	80				
							17	18	19		21		23	24	25	26	27			30				81						
										35			38	39	40	41			44	45										
							47								55	56		58	59	60							89	90		
						61	62					67		69	70	71		73	74	75							94	95		
CU5T-14A464-CD-019	34745-0019	34745-0801	END LATCH	1	34745-0501				4					9				13		15		76			79					
							17	18	19		21		23	24	25	26								81						
										35			38	39	40	41														
							47								55	56		58									89	90		
						61	62							69	70	71		73	74								94	95		
CU5T-14A464-CD-020	34745-0020	34745-0801	END LATCH	1	34745-0501				4									13		15		76			79					
							17	18	19		21		23	24	25	26								81						
										35			38	39	40	41														
							47								55	56		58									89	90		
						61	62							69	70	71		73	74								94	95		

GPCM 95-WAY RECEPTACLE ASSY SEALED PIN OUT SHEET

[illegible]



GPCM 95-WAY RECEPTACLE ASSY SEALED PIN OUT SHEET

CUSTOMER PART NUMBER	ASSEMBLY PART NUMBER	LEVER PART NUMBER	LEVER OPTION	KEY OPTION	OUTER SHROUD PART NUMBER	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION																						
						1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20			
CU5T-14A464-HD-002	34745-2002	34745-0801	END LATCH	2	34745-0502				4		6		8	9		11	12	13	14	15				77			80	
							17				21			24			27	28	29	30		81		83			85	
							32									41		43	44	45								
								48					53			56	57	58				86	87	88			90	
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75						95		
CU5T-14A464-HD-003	34745-2003	34745-0801	END LATCH	2	34745-0502				4		6		8	9			12	13	14	15				77			80	
							17				21				25	26	27	28	29	30		81		83			85	
							32							39	40	41		43	44	45								
						46	47	48					53			56	57	58				86	87	88			90	
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75						95		
CU5T-14A464-HD-004	34745-2004	34745-0801	END LATCH	2	34745-0502				4		6		8	9	10	11	12	13	14	15				76	77			80
							17				21			24			27	28	29	30						85		
							32									41		43	44	45								
																56								88			90	
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75				93			95	
CU5T-14A464-GD-003	34745-3003	34745-0802	TOP LATCH	2	34745-0502				4		6		8	9	10	11	12	13	14	15				77			80	
							17		19	20	21			24			27	28	29	30		81		83			85	
							32									41		43	44	45								
								48					53			56	57	58				86	87	88			90	
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75						95		
CU5T-14A464-HD-005	34745-2005	34745-0801	END LATCH	2	34745-0502				4		6		8	9		11	12	13	14	15				77			80	
							17				21			24			27	28	29	30		81		83			85	
							32									41		43	44	45								
						46		48					53			56	57	58				86	87	88			90	
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75						95		
CU5T-14A464-GD-004	34745-3004	34745-0802	TOP LATCH	2	34745-0502				4		6		8	9		11	12	13	14	15				77			80	
							17				21			24			27	28	29	30		81		83			85	
							32									41		43	44	45								
						46		48					53		55	56	57	58				86	87	88			90	
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75						95		
CU5T-14A464-GD-005	34745-3005	34745-0802	TOP LATCH	2	34745-0502				4		6		8	9		11	12	13	14	15				76	77			80
							17				21						27	28	29	30						85		
																		43	44	45								
															55	56								88			90	
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75				93			95	
CU5T-14A464-GD-006	34745-3006	34745-0802	TOP LATCH	2	34745-0502				4		6		8	9	10	11	12	13	14	15				77			80	
							17		19	20	21			24			27	28	29	30		81		83			85	
							32									41		43	44	45								
						46		48					53			56	57	58				86	87	88			90	
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75						95		
CU5T-14A464-HD-006	34745-2006	34745-0801	END LATCH	2	34745-0502				4				8	9		11	12	13	14	15				76	77			80
							17				21			24			27	28	29	30						85		
							32									41		43	44	45								
																56									89		90	
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75				93			95	



GPCM 95-WAY RECEPTACLE ASSY SEALED PIN OUT SHEET

CUSTOMER PART NUMBER	ASSEMBLY PART NUMBER	LEVER PART NUMBER	LEVER OPTION	KEY OPTION	OUTER SHROUD PART NUMBER	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION																				
CU5T-14A464-HD-007	34745-2007	34745-0801	END LATCH	2	34745-0502				4		6		8	9		11	12	13	14	15		76	77			80
							17				21			24			27	28	29	30					85	
							32									41		43	44	45						
																56								88		90
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75				93		95
CU5T-14A464-HD-008	34745-2008	34745-0801	END LATCH	2	34745-0502				4				8	9		11	12	13	14	15		76	77			80
							17				21			24			27	28	29	30					85	
							32									41		43	44	45						
																56								88		90
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75				93		95
CU5T-14A464-GD-007	34745-3007	34745-0802	TOP LATCH	2	34745-0502				4		6		8	9		11	12		14	15		76	77			80
							17				21			24			27	28	29	30					85	
							32									41		43	44	45						
															55	56								88		90
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75				93		95
CU5T-14A464-HD-009	34745-2009	34745-0801	END LATCH	2	34745-0502		2		4		6		8	9		11	12		14	15			77			80
							17				21			24			27	28	29	30	81		83		85	
							32									41		43	44	45						
									48				53			56	57	58				86	87	88		90
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75					95	
CU5T-14A464-HD-010	34745-2010	34745-0801	END LATCH	2	34745-0502				4		6		8	9		11	12		14	15			77			80
							17				21			24			27	28	29	30	81		83		85	
							32									41		43	44	45						
									48				53			56	57	58				86	87	88		90
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75					95	
CU5T-14A464-HD-011	34745-2011	34745-0801	END LATCH	2	34745-0502				4		6		8	9		11	12		14	15			77			80
							17				21			24			27	28	29	30	81		83		85	
							32									41		43	44	45						
									48				53		55	56	57	58				86	87	88		90
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75					95	
CU5T-14A464-GD-008	34745-3008	34745-0802	TOP LATCH	2	34745-0502				4		6		8	9		11	12		14	15			77			80
							17				21			24			27	28	29	30	81		83		85	
							32									41		43	44	45						
									48				53		55	56	57	58				86	87	88		90
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75					95	
CU5T-14A464-GD-009	34745-3009	34745-0802	TOP LATCH	2	34745-0502				4		6		8	9		11	12	13	14	15			77			80
							17				21			24			27	28	29	30	81		83		85	
							32									41		43	44	45						
						46		48					53			56	57	58				86	87	88		90
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75					95	
CU5T-14A464-HD-012	34745-2012	34745-0801	END LATCH	2	34745-0502				4		6		8	9		11	12		14	15		76	77			80
							17				21						27	28	29	30					85	
																		43	44	45						
						46									55	56								88		90
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75				93		95



GPCM 95-WAY RECEPTACLE ASSY SEALED PIN OUT SHEET

CUSTOMER PART NUMBER	ASSEMBLY PART NUMBER	LEVER PART NUMBER	LEVER OPTION	KEY OPTION	OUTER SHROUD PART NUMBER	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION																						
									4		6		8	9		11	12		14	15				76	77			80
CU5T-14A464-GD-010	34745-3010	34745-0802	TOP LATCH	2	34745-0502		17				21						27	28	29	30					85			
																43	44	45										
						46									55	56									88		90	
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75						93		95
DU5T-14A464-GC-000	34745-4001	34745-0801	END LATCH	3	34745-0503																							
DU5T-14A464-GC-001	34745-4001	34745-0801	END LATCH	3	34745-0503																							
DU5T-14A464-HC-000	34745-5001	34745-0802	TOP LATCH	3	34745-0503																							
DU5T-14A464-HC-001	34745-5001	34745-0802	TOP LATCH	3	34745-0503																							
DU5T-14A464-HC-002	34745-5002	34745-0802	TOP LATCH	3	34745-0503				4			7					13		15									
									19	20		22														83		
									34			37					43											
						61	62	63	64	65	66	67	68															
DU5T-14A464-HC-003	34745-5003	34745-0802	TOP LATCH	3	34745-0503				4			7					13		15									
									19	20		22																
									34			37																
						61	62	63	64		66	67	68															
DU5T-14A464-HC-004	34745-5004	34745-0802	TOP LATCH	3	34745-0503				3				8	9			12						76			80		
						16									25		27									85		
								33		35			38				42											
										50	51		53				57			60				86			90	
FU5T-14A464-GB-000	34745-6001	34745-0801	END LATCH	4	34745-0504																							



GPCM 95-WAY RECEPTACLE ASSY SEALED PIN OUT SHEET

CUSTOMER PART NUMBER	ASSEMBLY PART NUMBER	LEVER PART NUMBER	LEVER OPTION	KEY OPTION	OUTER SHROUD PART NUMBER	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION																				
FU5T-14A464-GB-001	34745-6001	34745-0801	END LATCH	4	34745-0504																					
FU5T-14A464-EB-000	34745-7001	34745-0802	TOP LATCH	4	34745-0504																					
FU5T-14A464-EB-001	34745-7001	34745-0802	TOP LATCH	4	34745-0504																					
FU5T-14A464-GB-002	34745-6002	34745-0801	END LATCH	4	34745-0504											11	12	13	14	15	76	77		80		
									19				24	25			28		30					85		
								33				37	38					43	44	45						
																57	58	59	60	86	87					
FU5T-14A464-GB-003	34745-6003	34745-0801	END LATCH	4	34745-0504	61	62	63	64									72	73	74	75	91			95	
									19										28		30					80
								33										43	44	45					85	
																57	58	59	60	86	87					
FU5T-14A464-GB-004	34745-6004	34745-0801	END LATCH	4	34745-0504												12	13			76			80		
									19									28		30					85	
								33				38					43									
								48									58	59								
FU5T-14A464-GB-005	34745-6005	34745-0801	END LATCH	4	34745-0504											11	12	13			76			80		
									19									28	29					85		
							32	33				38					43									
								48									58	59							86	
FU5T-14A464-GB-006	34745-6006	34745-0801	END LATCH	4	34745-0504																76			80		
									19				24	25			28	29						85		
							32	33				37	38				43									
								48									58	59						86		
FU5T-14A464-GB-007	34745-6007	34745-0801	END LATCH	4	34745-0504											11	12	13	14	15	76	77		80		
									19				24	25			28	29						85		
							32	33				37	38				43									
								48									58	59					86			
		63	64	65	66								72	73	74	75	91									




GPCM 95-WAY RECEPTACLE ASSY SEALED PIN OUT SHEET

CUSTOMER PART NUMBER	ASSEMBLY PART NUMBER	LEVER PART NUMBER	LEVER OPTION	KEY OPTION	OUTER SHROUD PART NUMBER	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION																						
FU5T-14A464-GB-008	34745-6008	34745-0801	END LATCH	4	34745-0504											11	12	13				76				80		
									19										28		30						85	
									33					38					43									
									48										58	59								
									63	64	65	66																
FU5T-14A464-GB-009	34745-6009	34745-0801	END LATCH	4	34745-0504											11	12	13				76				80		
									19										28		30						85	
									33					38					43	44	45							
																		57	58	59	60			86	87			
						61	62	63	64	65	66																	95
FU5T-14A464-GB-010	34745-6010	34745-0801	END LATCH	4	34745-0504											11	12	13	14	15		76	77			80		
									19					24	25				28		30						85	
									33					37	38				43	44	45							
																		57	58	59	60			86	87			
						61	62	63	64	65	66							72	73	74	75			91				95
FU5T-14A464-GB-011	34745-6011	34745-0801	END LATCH	4	34745-0504				4	5								13				76			79			
									19			21		23	24	25								81				
													37	38	39	40	41											
																55	56											
															69		71				74							
FU5T-14A464-GB-012	34745-6012	34745-0801	END LATCH	4	34745-0504											11	12	13				76				80		
									19										28								85	
									33					37	38					43	44	45						
																		57	58	59	60			86	87			
						61	62	63	64	65	66																	95
FU5T-14A464-GB-013	34745-6013	34745-0801	END LATCH	4	34745-0504				4		6	7				11	12					76	77		79			
																		28	29	30								
							32	33	34					38		40	41	42		44	45							
																56	57	58	59	60								
										65	66													91				
FU5T-14A464-EB-002	34745-7002	34745-0802	TOP LATCH	4	34745-0504				4	5	6	7				11	12					76	77					
																		28	29	30					83			
							32	33	34					38		40	41	42		44	45							
								48					52	53			56	57	58	59	60			86				
										65	66	67	68															
FU5T-14A464-HB-000	34745-8001	34745-0801	END LATCH	5	34745-0505																							
FU5T-14A464-HB-001	34745-8001	34745-0801	END LATCH	5	34745-0505																							






GPCM 95-WAY RECEPTACLE ASSY SEALED PIN OUT SHEET





CUSTOMER PART NUMBER	ASSEMBLY PART NUMBER	LEVER PART NUMBER	LEVER OPTION	KEY OPTION	OUTER SHROUD PART NUMBER	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION																								
FU5T-14A464-FB-000	34745-9001	34745-0802	TOP LATCH	5	34745-0505																									
FU5T-14A464-FB-001	34745-9001	34745-0802	TOP LATCH	5	34745-0505																									
FU5T-14A464-HB-002	34745-8002	34745-0801	END LATCH	5	34745-0505			3	4	5	6	7							13		15			76			80			
						16			19		21												81			84	85			
						31					36		38	39	40			43	44											
						46	47	48			51					56			59									90		
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75							94	95		
FU5T-14A464-HB-003	34745-8003	34745-0801	END LATCH	5	34745-0505			3	4	5	6	7							13		15			76			80			
						16			19		21											81			84	85				
						31					36			39	40			43	44											
						46	47	48			51					56			59								90			
						61	62	63	64	65	66	67	68	69	70	71	72	73	74	75							94	95		




SEE NOTE #11




SEE NOTE #11




END VIEW
SCALE 1:1



SIDE VIEW
SCALE 1:1



SCALE 1:1



SCALE 1:1

NOTES UNLESS OTHERWISE SPECIFIED

- PART MUST CONFORM TO THE FORD CONNECTOR SYSTEM DESIGN SPECIFICATION (SDS) REV 15 DATED 17SEPT2007
- PART MUST CONFORM TO USCAR SAE-2 REV5 DATED NOV2007
- ALL PLASTIC PARTS MUST HAVE MATERIAL IDENTIFICATION SYMBOLS CLEARLY MARKED, WHEREVER PACKAGE SIZE PERMITS
- ENGINEERING APPROVAL REQUIRED FOR ALL SOURCING AND TOOLING OF THIS PART
- FOR ENGINEERING APPROVED SOURCE SEE ENGINEERING RELEASE
- ENGINEERING APPROVAL OF SAMPLE FROM SUPPLIER IS REQUIRED PRIOR TO AUTHORIZATION OF PART PRODUCTION
- CHANGES IN DESIGN, COMPOSITION, OR PROCESSING OF THE PART, PREVIOUSLY APPROVED FOR PART PRODUCTION REQUIRES PRIOR ENGINEERING APPROVAL
- GENERAL TOLERANCES:
LINEAR: PER DIN 16901-130
ANGULAR: ±3°
- 0.3 MAXIMUM RADIUS PERMISSIBLE ON EDGES AND FILLETS SHOWN AS SHARP FOR PLASTIC PARTS
- PARTS ARE TO BE FREE OF SCRATCHES, DISCOLORATIONS, SALT RESIDUE OR OTHER IMPERFECTIONS THAT MAY AFFECT FUNCTION OR FIT OF PART
- LETTERING SHALL BE AS LARGE AS POSSIBLE, LOCATED ON RECESSED PAD APPROXIMATELY AS SHOWN. THIS INCLUDES MOLD CAVITY ID, SERIES NUMBER, MANUFACTURING LOCATION, MATERIAL DESIGNATION, VENDOR ID AND CUSTOMER ID.
- PART MUST MATE WITH MOLEX CONNECTOR SERIES 34745 AND 34746
- PART IS SHIPPED SEPARATELY
- 20% MAXIMUM REGRIND ALLOWED

B2	NX-REMASTERING
B1	SAP NOTICE #10591650 ECN #UUAU2013-1639 KDEKOSKI 04/17/13
B	SAP NOTICE #TBD ECN #UUAU2011-0493 KDEKOSKI 08/29/12
A1	SAP NOTICE #10490158 ECN #UUAU2011-0598 JDUNAJ 01/24/11
A	SAP NOTICE #10483555 ECN #UUAU2011-0371 JDUNAJ 11/24/10
REV	DESCRIPTION

QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
 = 0	EC NO: 122915 DRWN: VYARAPPA CHKD: APROFIT REV: APROFIT	2017/09/21	2017/10/06	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION UNITS	SCALE										
 = 0					mm	2:1										
 = 0					DRWN BY	DATE										
 = 0					JDUNAJ	2010/10/18										
 = 0					ANGULAR TOL ± °	CHK'D BY	DATE		90 DEG LARGE VOLUME WDC G-PCM CONNECTOR END LATCH							
 = 0					4 PLACES ±	KDEKOSKI	2010/10/22									
 = 0					3 PLACES ±	APPR BY	DATE						PRODUCT CUSTOMER DRAWING			
 = 0					2 PLACES ±	RBAUMAN	2010/12/07									
 = 0					1 PLACE ±	DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES	MATERIAL NUMBER		CUSTOMER			
= 0					0 PLACES ±	D				34745	347450905		FORD			
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER						
	B2					SD-34745-905		PSD	001	1 OF 1						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34745-0001](#)