




REF -50 OPTION SCREW
(WHERE APPLICABLE)




NOTES:

1. MATERIAL: SEE TABLE
2. INCH DIMENSIONS ARE SHOWN IN BRACKETS [XXX].
3. "XX" REFERS TO THE QUANTITY OF CIRCUITS.
4. ALL COMPONENTS ARE ROHS COMPLIANT.




4 CIRCUIT SHOWN



XX	SCREW&WASHER, 6-32X.250, PAN, PH/SL (-50 OPTION)	STEEL	ZN, CLEAR CHROMATE
XX	SCREW, 6-32X.250, BHD, PHIL-SLOT (-49 OPTION)	BRASS	NICKEL
XX	SCREW, 6-32X.250, BHD, PHIL-SLOT (STANDARD)	STEEL	ZN, CLEAR CHROMATE
XX	TERMINAL, SOLDER TURRET	BRASS	TIN
XX	MOUNTING PLATE	BRASS	NICKEL
1	INSULATOR, SR, W/MTG	THERMOPLASTIC	BLACK
M QTY	DESCRIPTION	MATERIAL	FINISH

INITIAL RELEASE EC NO: ETC2007-0073 DRAWN: EHILE 2006/09/28 CHKD: JMACNEIL 2006/09/28 APPR: JMACNEIL 2006/09/29	DESCRIPTION	REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION 	
				mm	INCH	DRAWN BY EHILE	DATE 2006/09/13	9.53MM [.375] SR BTS ASSY, INSULATED TURRET TERMINAL W/MTG			
				4 PLACES ±---	±---	CHECKED BY JMACNEIL	DATE 2006/09/13				
				3 PLACES ±---	±.005						
				2 PLACES ±0.13	±.01	APPROVED BY JMACNEIL	DATE 2006/09/13	MOLEX MOLEX INCORPORATED			
1 PLACE ±0.25	±---										
ANGULAR ± 2 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-38720-010		1 OF 2					
		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38720-3205](#)