

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200270364](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) Single-Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 0.25mm² PVC Cable, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
Series [120027](#)
Connector End A Nano-Change (M8)
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Nano-Change \(M8\) Products](#)
Product Name Nano-Change (M8)
Protocol N/A
Region Europe
Type Single Ended
UPC 883906026431

Physical

Cable Diameter 5.08mm (.200")
Cable Length 1.0m (3.28')
Color - Cable Jacket Black
Coupling Style Threaded
Gender Male-Pigtail
Keyway A-coded
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PUR
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Fluoro-elastomer
Material - Plating Mating Gold
Net Weight 98.000/g
Orientation Straight to Pigtail
Poles 3
Temperature Range - Operating -25°C to +80°C
Wire Size AWG 24
Wire/Cable Type UL 2464

Electrical

Current - Maximum per Contact 3.0A
Voltage - Maximum 60V AC / 75V DC

Material Info

Engineering Number 403006E02M010

Reference - Drawing Numbers

Sales Drawing SD-120086-002-001



EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant with
Exemption 3

Not Contained

Search Parts in this Series

[120027](#) Series

This document was generated on 09/01/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120027-0364