

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200658972](#)
Status: **Active**
Overview:
Description: Micro-Change (M12) Single-Ended Cordset, 8 Poles, Female (Straight) to Pigtail, 24 AWG, 10.0m (32.81') Length

General	
Product Family	Industrial Cordsets
Series	120065
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	microchange_m12_connectors
Product Name	Micro-Change (M12)
Type	Single Ended
UPC	78172534420
Physical	
Cable Diameter	6.10mm (.240")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-coded
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	519.410/g
Orientation	Straight to Pigtail
Poles	8
Temperature Range - Operating	-25°C to +85°C
Wire Size AWG	24
Wire/Cable Type	Shielded PVC
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	30V
Material Info	
Engineering Number	808000S19M100
Reference - Drawing Numbers	
Sales Drawing	1200658605-000

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[120065](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200658972