

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200860464

Status:

Active

Overview:

Brad Nano-Change (M8) Products

Description:

Nano-Change (M8) Single-Ended Cordset, 3 Poles, Female (90°) to Pigtail, with PNP LED Sensors, 0.34mm² PUR/PVC Cable, 5.0m (16.40') Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	120086
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Region	Europe
Type	Single Ended
UPC	78172553796
Physical	
Cable Diameter	4.32mm (.170")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-coded
LED Indicator	PNP Sensors
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	154.640/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-30° TO +80°C
Wire Size AWG	N/A
Wire/Cable Type	E152210
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC/DC
Material Info	
Engineering Number	4030P1P03M050
Reference - Drawing Numbers	
Sales Drawing	SD-120086-022-001

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Bisphenol-A

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

ZZCERT_CE - Declaration of Conformity

CER_4000380995_00_000.pdf

Search Parts in this Series

120086 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200860464